



DURST SmartWasher Model DSW-123

The SmartWasher Fully Complies with Australian OH&S Regulations and is a patented non-hazardous, bioremediating parts cleaning system. The SmartWasher uses a warm aqueous degreasing solution called OzzyJuice. Both the SmartWasher and the OzzyJuice solutions have passed a number certifications and approvals. Overall, the SmartWasher reduces the release of VOC's, eliminates liquid hazardous waste and helps save our environment while protecting the health & wellbeing of your employees.

New Mobile Model



Our New Mobile model. DSW-123 **Electronic controls** and a **standard sink** is IP65 Rated and make this unit ideal for almost any cleaning job.



SmartWasher Certificates and Approvals



AQMD Certified
DSW-SW3 Truck Grade OzzyJuice.
DSW-SW6-8 Weapons Aviation Grade OzzyJuice.



Authorization to Mark



Declaration of Conformity



Test Certificate in Compliance with the Device Safety Act



Test Certificate in Compliance with the Device Safety Act
National Sanitation Foundation. DSW-SW3, DSW-SW6-8 OzzyJuice



Product Safety Certificate



DURST MOTOR & ELECTRIC INDUSTRIES P/L 189-189B ST JOHNS RD, GLEBE NSW 2037
Ph: 02 9660 1755 Fax: 02 9692 0251 Email: sales@durst.com.au Web: www.durst.com.au

DWS-123 New Spec V1007.doc

DURST SmartWasher Model DSW-123

Specifications DSW-123

- Overall dimensions**
L x W x H:
- 1090mm x 685mm x 1050mm
- Inside sink dimensions:**
- 600mm x 520mm x 204mm
- Shipping dimensions:**
- 1130mm x 712mm x 1130mm
- Material:**
- Blowmolded high density polyethylene for durability and consistent quality
- Pump capacity:**
- 93.75W; 170 GPH at 1 foot; sump intake
- Electrical:**
- 240v, 50 Hz
- Heater:**
- 1000 watt industrial heater
- Weight:**
- 33Kg empty;
 - Holds 250Kg. load
- Features:**
- ON/OFF control, side mounted
 - Flow timer with 10 and 30 minute increments
 - Flow-through parts brush
 - User regulated independent flow control from brush or nozzle.
 - Thermostat maintains fluid at 42°C (adjustable to 46°C)
 - Does not damage rubber or neoprene gaskets & seals
 - Warm cleaning solution
- Indicators:**
- Low fluid level indicator (red)
 - Standby/ready indicator (green)
 - Power indicator (green)
- Options Available :**
- Peel able filters
- Filtration:**
- User changeable and disposable without hand tools or special equipment
 - Microbe impregnated
 - Filtration to 50 microns
- Cleaning solution:**
- Aqueous based surfactant cleaner
 - **NO** flashpoint
 - PH neutral, biodegradable
 - Non-toxic, no caustic, non-flammable, nonhazardous
 - **NO** VOCs, phosphates, formaldehyde, biocides or solvents
- Microbe treatment:**
- Environmental-shock resistant; preserved for minimum 18-month shelf life
 - Naturally occurring, non-pathogenic microbes



DURST MOTOR & ELECTRIC INDUSTRIES P/L 189-189B ST JOHNS RD, GLEBE NSW 2037
Ph: 02 9660 1755 Fax: 02 9692 0251 Email: sales@durst.com.au Web: www.durst.com.au

DWS-123 New Spec V1007.doc